Page 1 / 1



## Intended use

Mipa Anti-Silikon-Zusatz (anti silicone additive) avoids cratering and improves the flow when coating surfaces with residues of silicone, polish, wax and grease. Suitable for Mipa 2K paints (Mipa OC, PUR HS, all Mipa 2K clearcoats) and Mipa paints based on synthetic resins.

Quantity to add: 2 up to max. 5% Mipa Anti-Silicone additive to base paint or to base paint after addition of hardener in case of 2K paint materials.

The use of Mipa Anti-Silikon-Zusatz has no influence on drying times.

## Processing instructions

::

Mixing ratio

by weight (lacquer : anti silicone additive) add at most 2 - max. 5 % to the basic paint



Hardener

see tech sheet basic product



Pot life

see tech sheet basic product



**Thinner** 

see tech sheet basic product

**Storage:** at least 3 years in unopened original container

VOC Regulation: VOC as packaged:

less exempt solvents 857 g/l / 7.1 lb/gl with exempt solvents 857 g/l / 7.1 lb/gl

Always check local VOC laws to ensure that the use of Mipa products is compliant in your area.

**Special notes:** The use of Mipa Anti-Silikon-Zusatz has no influence on drying times.

For professional use only. Not for sale to or use by the general public.

Before opening the packages be sure you understand the warning Messages on the Labels and

Safety Data Sheets of all components since the mixture will have the hazards of all of its parts. The manufacturer recommends the use of an air supplied Respirator when

exposed to vapors or spray mist.

Medical Response:

Emergency Medical or Spill Control Information 011 49(0)700 24112112 (MIP) US Emergency Phone Number (for transportation incidents only) 1-800-535-5053

(Infotrac)

**Exclusive Importer: Fleetwood Products** 

3 American Way, Suite 15, Spotswood, NJ 08884 www.mipa-usa.com fleetwood@mipa-usa.com. 732-416-9590 Phone, 732-416-9592 Fax.

Version: US 0418