

GENERAL INFORMATION

PF345W Rapid Surfer White can be used for small to medium repair work over multiple automotive substrates. The sanding surfer can be applied directly on e-Coat primed parts and does not require an additional guide coat due to its glossy appearance after drying.

MIXING RATIO



1 : 1 Surfer : Thinner + 25% Hardener on volume

Please note: The surfer and thinner can be pre-mixed. The hardener needs to be added to the spray mixture just before application, due to the limited pot life.

COMPONENTS



TH345 Rapid Surfer Thinner
H345 Rapid Surfer Hardener

GUN SETUP



	NOZZLE (MM)	AIR PRESSURE (BAR / PSI)
HVLP	1,3-1,4	1,5 / 22
HE	1,3-1,4	1,8 / 26

ADDITIVES



APPLICATION



2 - 3 coats, maximum around 100-120 µm

POTLIFE



15 minutes

FLASH OFF AND DRY TIMES



	AIR DRY 20°C / 68°F		FORCED DRY 60°C / 140°F
Flash off	2 minutes	Flash off	-
Dust free	15 - 20 minutes	Dust free	-
Dry to handle	15 - 20 minutes	Dry to handle	-
Dry to tape	20 - 40 minutes	Dry to tape	-
Dry to sand	20 - 40 minutes	Dry to sand	-
Dry to polish	-	Dry to polish	-

High film builds and low temperatures can increase dry times. Drying times may be slightly longer with temperatures below 20°C and low humidity.

SURFACE PREPARATION



Preclean the surface with TD20 Silicone Remover. Wipe on and wipe dry. Sand surface with P180-P240 grit abrasive. Remove all sanding debris with compressed air. Sanding vacuum and clean with TD20 Silicone Remover. Wipe on and wipe dry.



Final sanding with P600 and P800 before application of Basecoat.

Mask entire vehicle to eliminate unwanted overspray.

SUBSTRATES



PF345W Rapid Surfer White should only be applied over well sanded/scuffed and degreased primed bare steel and primed aluminium.

Well sanded GRP, polyester fillers, OEM primer and old paint systems in good condition.

Use PW170 Washprimer recommended for maximum durability and rust protection.

NEXT LAYER



W00 - W999 Octobase Eco Plus System
B00 - B999 Octobase System

INFRARED DRYING



After full flash off and at proper distance	
Half-bake	2 min 60°C
Full-bake	1 min 70°C
See IR Manufacturer information	

SUBSTRATES PLASTIC



Substrate	PF345G Rapid Surfer
ABS	It has good direct to ABS adhesion, no need to use the PA65 1K Plastic Primer.
PP/EPDM	Spray the PA65 1K Plastic Primer

PHYSICAL DATA

EU REGULATIONS PF345W Rapid Surfacers White	
VOC Code	2004/42/II B(c)(540)462
Product sub category (according directive 2004/42/EC) and max VOC content (ISO 11890-1/2) of the ready to use product.	IIB/c. Primer - Surfacers/filler and general (metal) primer. EU limit values: 540 g/l. (2007) This product contains a maximum of 462 g/l VOC.
Chemical Base	2K Urethane Primer
Physical Properties	Viscosity (RTS)
	12 - 14 Dincup 4 / 20°C
	Specific Gravity (kg/l)
	1,23
	Flash Point Closed Cup
	28°C / 82,4°F
	Volume % Solids
	46,3
	Economy
	185 ft²/Gal @ 4 mil
	18,5 m²/L/100 µm
	Gloss
	Egg Gloss
	Colour
	White

PROTECTION



Use suitable respiratory protection (*fresh air supply respirator is strongly recommended*).

For more detailed information please visit the following link for the Safety Data Sheet:

[SDS Octoral](#)

CLEANUP



Gun Cleaner

STORAGE/SHELF LIFE



The up-to-date shelf life overview can be found by clicking on the following link:

[Shelf life overview Octoral](#)

NOTES

